


# Technical Data Sheet LINER CLOSURE

Caps_PL-01
Page. 1 of 2
06.01.2014 г.
Revision 2

### **Description:**

Twist off cap with folded inside tamper-evident, 28mm PP, 3 threads, 120 pins, 10 bridges. The closures are produced for packaging of liquids under pressure in bottles with neck  $\emptyset$  28mm , PCO/BPF, for one way use.





#### 2. Основни технически изисквания за капачките

Shell material	Polypropylene (PP)		
Liner material	Plastizol		
Color	According to the Technological card of the approved		
	sample.		
Print	According to the Technological card of the approved		
	sample.		
Closure weight with the liner , g	$2.95 \pm 0.05 \text{ g}$	Controlled	
Temper evident height, mm	$5.2 \pm 0.1 \text{ mm}$	Controlled	
Closing torque, Lb	18 - 28 Lb	Controlled	
Opening torque	8 - 15 Lb	Controlled	
Temper evident tear off strength, Lb	7 - 15 Lb	Controlled	
Closure measurements	According to the drawing	Controlled	

### 3. Packaging and labelling

The closures are packed with cardboard box, produced corrugated cardboard with PE bag inside.

- **3.1.1** Dimensions of the cardboard box: 590/390/400
- **3.1.2** Type of the cardboard: 5 layers
- **3.1.3** Quantity of closures per cardboard box: 4300 pcs.
- **3.1.4** The cardboard boxes should be 25 pcs per pallet
- **3.1.5** Dimensions of the pallet (/1200/1000/140)
- **3.1.6** The ready pallet should be stretched with stretch film
- 3.2 Each cardboard box should be labelled with the following information:
- GOTMAR, address, e-mail
- Article type



# Technical Data Sheet LINER CLOSURE


 Caps\_PL-01

 Page. 2 of 2

 06.01.2014 ε.

Revision 2

- Closure color
- Type of the logo
- Lot
- Production date sign from the technician
- Quantity number of closures per box
- Serial number of the box



#### 4. Storage

- 4.1 Dry place, out of contaminations and direct sunlight
- 4.2 Recommended storage temperature of the closures: 5°C ÷ 35°C max
- 4.3 Minimum ambient temperature 16°C
- 4.4 The closures should be thermal equilibrated with the ambient temperature of the workshop at least 48 hours prior the use (16°C÷25°C).

Upon occured change of the recommended limits of the ambient temperature in period more than 10 days, before usage the closures should be with mode "Caution" for the client.

- 4.5 Maximum storage period from delivery till the use of the closure -12 months.
- 4.6 Should not be lied more than two pallets one above another.

Laboratory Gotmar